

# Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # 7305-207

Outdoor Station, Multi Party Line, FM-approved for Division 2 areas, NEMA 4X rated, 24V dc operation; consists of: Amplifier (Model 701-307) and Enclosure (Model 7335-002)



## General

Color	Gray
Material	Steel / GRP
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Outdoor

## Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5
Height	14.6 in
Weight	16.4 lb
Width	10.9 in

## Electrical Ratings

Signal	33 Ohm
--------	--------

## Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

## Product Assets

[Brochures - Page/Party® Solutions Brochure](#)  
[Brochures - Page/Party® Accessories Guide](#)  
[Installation Manuals - 700 Series 24 VDC Page/Party® System Design and Installation](#)