

Plant Paging Station

By GAI-Tronics
Catalog # 750-402

Indoor Speaker Amplifier 24 VDC, NRTL Listed for USA and Canada, Class I, Div. 2, Groups A, B, C, D; consists of: Amplifier (Model 751-002), Enclosures (Model 702-002).



General

Color	Gray
Material	Steel
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Indoor

Dimensions

Cubic Capacity	334.611 cu.in
Depth	5.1
Height	8.1 in
Weight	11.1 lb
Width	8.1 in

Electrical Ratings

Signal	33 Ohm
--------	--------

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Brochures - Page/Party® Solutions Brochure](#)
[Brochures - Page/Party® Accessories Guide](#)
[Installation Manuals - 700 Series 24 VDC Page/Party® System Design and Installation](#)