



Plant Paging Amplifier

By GAI-Tronics
Catalog # 751-002VC

Speaker Amplifier, 24 VDC with remote volume control.



General

Color	Gray
Material	Steel
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Indoor

Dimensions

Cubic Capacity	196.83 cu.in
Depth	3
Height	8.1 in
Weight	5 lb
Width	8.1 in

Electrical Ratings

Signal	33 Ohm
--------	--------

Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Brochures - Page/Party® Solutions Brochure](#)
[Brochures - Page/Party® Accessories Guide](#)
[Installation Manuals - Volume Level Control Receiver Assembly](#)
[Instruction Sheet](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
GTC-751-002VC-SPEC-EN | REV 7/2023