

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # [780-002](#)

Indoor Hazardous Area Station, Single-Party Line 24 VDC operation. NRTL approved for use in USA and Canada:- Class I, Div 1, Groups C and D - Class II, Div. 1, Groups E, F and G - Class III, Div. 1



General

Color	Gray
Material	Aluminum
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Indoor

Dimensions

Cubic Capacity	579.544 cu.in
Depth	5.6
Height	13.1 in
Weight	27 lb
Width	7.9 in

Electrical Ratings

Signal	33 Ohm
--------	--------

Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 1

Product Assets

[Brochures - Page/Party® Solutions Brochure](#)
[Brochures - Page/Party® Accessories Guide](#)
[Installation Manuals - 700 Series 24 VDC Page/Party® System Design and Installation](#)
[Installation Manuals - Explosion-proof Handset Stations \(Model 780-002, 785-002, 7805-002, and 7855-002 24 V DC\)](#)