

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # [7855-002](#)

Outdoor Hazardous Area Station, Multi-Party Line, 24 VDC operation. NRTL certified for use in US and Canada, - Class I, Div. 1, Groups C and D; - Class II, Div. 1, Groups E, F, and G; - Class III, Div. 1, Consisting of: Amplifier (Model 7805-002) and Enclosure (Model 10444-003)



General

Color	Gray
Material	Aluminum / GRP
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Outdoor

Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5
Height	14.6 in
Weight	35 lb
Width	10.9 in

Electrical Ratings

Signal	33 Ohm
--------	--------

Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 1

Product Assets

[Brochures - Page/Party® Solutions Brochure](#)
[Brochures - Page/Party® Accessories Guide](#)
[Installation Manuals - 700 Series 24 VDC Page/Party® System Design and Installation](#)
[Installation Manuals - Explosion-proof Handset Stations \(Model 780-002, 785-002, 7805-002, and 7855-002 24 V DC\)](#)

Related Products

[785-002 - Plant Paging/Intercom Station](#)