



## Plant Paging Station

By GAI-Tronics  
Catalog # [810-310D1R0](#)

ICS Indoor Speaker Amplifier Station - 100-240VAC - UL Class I, Div. 2 - 70/100V speaker output - Orange finish



### General

Color	Orange
Material	Steel
Output Level Speaker	70/100 V
Series	ICS
Signal Type	Analog
Type	<ul style="list-style-type: none"><li>• Speaker Amplifier Station</li><li>• Indoor Speaker Amplifier Stations</li></ul>
Weather Rating	NEMA Type 12

### Dimensions

Cubic Capacity	610.90965 cu.in
Depth	5.07 in
Height	14.5 in
Weight	11 lb
Width	8.31 in

### Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

### Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station Literature - ICS Amplifiers](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
GTC-810-310D1R0-SPEC-EN | REV 7/2023