



## Plant Paging Station

By GAI-Tronics  
Catalog # [810-710D1R0](#)

ICS Indoor Speaker Amplifier Station - 24VDC - UL Class I, Div. 2 - 70/100V speaker output - Orange finish



### General

|                      |   |
|----------------------|---|
| Color                | Orange  |
| Material             | Steel   |
| Output Level Speaker | 8 Ohm   |
| Series               | ICS   |
| Signal Type          | Analog  |
| Type                 | <ul style="list-style-type: none"><li>• Speaker Amplifier Station</li><li>• Indoor Speaker Amplifier Stations</li></ul> |
| Weather Rating       | NEMA Type 12  |

### Dimensions

|                |                 |
|----------------|-----------------|
| Cubic Capacity | 610.90965 cu.in |
| Depth          | 5.07 in         |
| Height         | 14.5 in         |
| Weight         | 11 lb           |
| Width          | 8.31 in         |

### Electrical Ratings

|                |        |
|----------------|--------|
| Signal         | 33 Ohm |
| Voltage Rating | 24 VDC |

### Certifications and Compliance

|                     |          |
|---------------------|----------|
| Certified Listed    | UL       |
| Hazardous Rating(s) | UL Div 2 |

### Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station Literature - ICS Amplifiers](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
GTC-810-710D1R0-SPEC-EN | REV 7/2023