

# Plant Paging Station

By GAI-Tronics  
Catalog # 810-310B100

ICS Indoor Speaker Amplifier Station - 100-240VAC - CE Safe area - 8-ohm speaker output - Orange finish



## General

Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	Speaker Amplifier Station
	Indoor Speaker Amplifier Stations
Weather Rating	NEMA Type 12

## Dimensions

Cubic Capacity	610.90965 cu.in
Depth	5.07 in
Height	14.5 in
Weight	11 lb
Width	8.31 in

## Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

## Certifications And Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

## Product Assets

[Installation Manuals - ICS Page/Party® Handset/Speaker Amplifier Station](#)  
[Literature - ICS Amplifiers](#)