

Plant Paging Station

By GAI-Tronics
Catalog # 810-310D100

ICS Indoor Speaker Amplifier Station - 100-240VAC - UL Class I,
Div. 2 - 8-ohm speaker output - Orange finish



General

Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	Speaker Amplifier Station
	Indoor Speaker Amplifier Stations
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	610.90965 cu.in
Depth	5.07 in
Height	14.5 in
Weight	11 lb
Width	8.31 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

- [Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)
- [Literature - ICS SmartSeries Equipment Overview](#)
- [Literature - ICS Amplifiers](#)