

# Plant Paging Station

By GAI-Tronics  
Catalog # 810-320D1R0

ICS Indoor Speaker Amplifier Station - 100-240VAC - UL Class I,  
Div. 2 - 70/100V speaker output with VLC - Orange finish



## General

Color	Gray
Material	Steel
Output Level Speaker	70/100 V
Power	24 W
Series	ICS
Signal Type	Analog
Type	Speaker Amplifier Station
	Indoor Speaker Amplifier Stations
Weather Rating	NEMA Type 12

## Dimensions

Cubic Capacity	610.90965 cu.in
Depth	5.07 in
Height	14.5 in
Weight	11 lb
Width	8.31 in

## Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

## Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

## Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)  
[Literature - ICS Amplifiers](#)