

Plant Paging Station

By GAI-Tronics
Catalog # 810-390A1A0

ICS SmartSeries Indoor Speaker Amplifier Station, 100-240 VAC,
UL Safe area, Eight speaker output with individual monitoring,
SmartSeries features, Orange finish, PCBA tropicalization



General

Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	610.90965 cu.in
Depth	5.07 in
Height	14.5 in
Weight	11 lb
Width	8.31 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

Product Assets

[Installation Manuals - ICS - Page/Party® Eight-Channel Speaker Monitoring/Distribution Amplifier](#)
[Literature - ICS Eight-Speaker Station](#)