



Plant Paging Station

By GAI-Tronics
Catalog # [810-710D2S0](#)

ICS Indoor Speaker Amplifier Station - 24VDC - UL Class I, Div. 2
- 70/100V speaker output - Gray finish, PCBA tropicalization

Features

Industrial Communication System

General

Catalog Number	810-710D2S0
Color	Gray
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	- Speaker Amplifier Station - Indoor Speaker Amplifier Stations
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	610.90965 cu.in
----------------	-----------------

Depth	5.07 in
Height	14.5 in
Weight	11 lb
Width	8.31 in

Electrical Ratings

Input Voltage	24 VDC
Signal	33 Ohm
Voltage Rating	24 VDC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)
[Literature - ICS Amplifiers](#)
[Specifications - 810710D2S0](#)