

## Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # 811-111D1S0

ICS Indoor Handset/Speaker Single-party Station, 100-240 VAC, UL Class I, Div. 2, 70/100V speaker output, Orange finish, 6' PVC handset cord, PCBA tropicalization



### General

|                      |                        |
|----------------------|------------------------|
| Color                | Orange                 |
| Material             | Steel                  |
| Output Level Speaker | 70/100 V               |
| Power                | 24 W                   |
| Series               | ICS                    |
| Signal Type          | Analog                 |
| Type                 | Single Party           |
|                      | 70/100V speaker output |
| Weather Rating       | NEMA Type 12           |

### Dimensions

|                |                |
|----------------|----------------|
| Cubic Capacity | 985.6491 cu.in |
| Depth          | 8.18 in        |
| Height         | 14.5 in        |
| Weight         | 12 lb          |
| Width          | 8.31 in        |

### Electrical Ratings

|                |             |
|----------------|-------------|
| Signal         | 33 Ohm      |
| Voltage Rating | 100-240 VAC |

### Certifications And Compliance

|                     |          |
|---------------------|----------|
| Certified Listed    | UL       |
| Hazardous Rating(s) | UL Div 2 |

### Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)  
[Literature - ICS Indoor Stations](#)