



# Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # [811-111D200](#)

ICS Indoor Handset/Speaker Single-party Station, 100-240 VAC, UL Class I, Div. 2, 8-ohm speaker output, Gray finish, 6' PVC handset cord



## Features

Industrial Communication System

## General

Catalog Number	811-111D200
Color	Gray
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	<ul style="list-style-type: none"><li>Single Party</li><li>8-ohm speaker output</li></ul>
Weather Rating	NEMA Type 12

## Dimensions

Cubic Capacity	985.6491 cu.in
----------------	----------------

Depth	8.18 in
Height	14.5 in
Weight	12 lb
Width	8.31 in

## Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

## Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

## Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)  
[Literature - ICS Indoor Stations](#)  
[Specifications - 811111D200](#)