

## Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # 811-141D2A0

ICS SmartSeries Indoor Handset/Speaker Single-party Station, 100-240 VAC, UL Class I, Div. 2, 8-ohm speaker output with SmartVolume, SmartSeries features, Gray finish, 6' PVC handset cord, PCBA tropicalization



### General

Color	Gray
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Type	Single Party
	8-ohm speaker output with SmartVolume
Weather Rating	NEMA Type 12

### Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	12 lb
Width	8.31 in

### Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

### Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)  
[Literature - ICS Indoor Stations](#)