

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # 811-211B100

ICS Indoor Handset/Speaker Single-party Station, 100-240 VAC,
CE Safe area, 8-ohm speaker output, Headset jack, Orange finish,
6' PVC handset cord



General

Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	Single Party
	Headset Jack
	8-ohm speaker output
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	12 lb
Width	8.31 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

Product Assets

[Installation Manuals - ICS Page/Party® Handset/Speaker Amplifier Station](#)
[Literature - ICS Indoor Stations](#)