



Plant Paging/Intercom Station

By GAI-Tronics
Catalog # [815-121D100](#)

ICS Indoor Handset/Speaker Multi-party Station, 100-240 VAC, UL Class I, Div. 2, 8-ohm speaker output with VLC, Orange finish, 6' PVC handset cord



General

| | |
|----------------------|---|
| Color | Orange |
| Material | Steel |
| Output Level Speaker | 8 Ohm |
| Series | ICS |
| Signal Type | Analog |
| Type | <ul style="list-style-type: none">Multi-Party8-ohm speaker output with VLC |
| Weather Rating | NEMA Type 12 |

Dimensions

| | |
|----------------|----------------|
| Cubic Capacity | 985.6491 cu.in |
| Depth | 8.18 in |
| Height | 14.5 in |
| Weight | 12 lb |
| Width | 8.31 in |

Electrical Ratings

| | |
|----------------|-------------|
| Signal | 33 Ohm |
| Voltage Rating | 100-240 VAC |

Certifications and Compliance

| | |
|---------------------|----------|
| Certified Listed | UL |
| Hazardous Rating(s) | UL Div 2 |

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station Literature - ICS Indoor Stations](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
GTC-815-121D100-SPEC-EN | REV 7/2023