

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # [815-151D100](#)

ICS SmartSeries Indoor Handset/Speaker Multi-party Station, 100-240 VAC, UL Class I, Div. 2, 8-ohm speaker output with SmartVolume, SmartSeries features with RTU input/output, Orange finish, 6' PVC handset cord



General

Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Series	ICS SmartSeries
Signal Type	Analog
Type	<ul style="list-style-type: none"> Multi-Party SmartSeries with RTU input/output 8-ohm speaker output with SmartVolume
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	12 lb
Width	8.31 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station Literature - ICS Indoor Stations](#)