



## Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # [815-161B100](#)

ICS SmartSeries Indoor Handset/Speaker Multi-party Station, 100-240 VAC, CE Safe area, 8-ohm speaker output with SmartVolume, SmartSeries features with Alternate Page selector, Orange finish, 6' PVC handset cord



### General

Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Series	ICS SmartSeries
Signal Type	Analog
Type	<ul style="list-style-type: none"><li>Multi-Party</li><li>SmartSeries with Alternate Page selector</li><li>8-ohm speaker output with SmartVolume</li></ul>
Weather Rating	NEMA Type 12

### Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	12 lb
Width	8.31 in

### Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications and Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

### Product Assets

[Installation Manuals - ICS Page/Party® Handset/Speaker Amplifier Station](#)  
[Literature - ICS Indoor Stations](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
GTC-815-161B100-SPEC-EN | REV 7/2023