

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # 815-141B1S0

ICS SmartSeries Indoor Handset/Speaker Multi-party Station, 100-240 VAC, CE Safe area, 70/100V speaker output, SmartSeries features, Orange finish, 6' PVC handset cord, PCBA tropicalization



General

Color	Orange
Material	Steel
Output Level Speaker	70/100 V
Power	24 W
Series	ICS SmartSeries
Signal Type	Analog
Type	Multi-Party
	70/100V speaker output
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	12 lb
Width	8.31 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

Product Assets

[Installation Manuals - ICS Page/Party® Handset/Speaker Amplifier Station](#)
[Literature - ICS Indoor Stations](#)