



Plant Paging/Intercom Station

By GAI-Tronics
Catalog # 815-151D1A0

ICS SmartSeries Indoor Handset/Speaker Multi-party Station, 100-240 VAC, UL Class I, Div. 2, 8-ohm speaker output with SmartVolume, SmartSeries features with RTU input/output, Orange finish, 6' PVC handset cord, PCBA tropicalization



Features

Industrial Communication System

General

Catalog Number	815-151D1A0
Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Type	<ul style="list-style-type: none">Multi-PartySmartSeries with RTU input/output8-ohm speaker output with SmartVolume
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	12 lb
Width	8.31 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)
[Literature - ICS Indoor Stations](#)
[Specifications - 815151D1A0](#)