

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # 815-151D1R0

ICS SmartSeries Indoor Handset/Speaker Multi-party Station, 100-240 VAC, UL Class I, Div. 2, 70/100V speaker output, SmartSeries features with RTU input/output, Orange finish, 6' PVC handset cord



General

Color	Orange
Material	Steel
Output Level Speaker	70/100 V
Power	24 W
Series	ICS SmartSeries
Signal Type	Analog
Type	Multi-Party
	SmartSeries with RTU
	70/100V speaker output
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	12 lb
Width	8.31 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)
[Literature - ICS Indoor Stations](#)