

# Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # [815-161D200](#)

ICS SmartSeries Indoor Handset/Speaker Multi-party Station,  
100-240 VAC, UL Class I, Div. 2, 8-ohm speaker output with  
SmartVolume, SmartSeries features with Alternate Page selector,  
Gray finish, 6' PVC handset cord



## Features

Industrial Communication System

## General

Catalog Number	815-161D200
Color	Gray
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Type	<ul style="list-style-type: none"><li>• Multi-Party</li><li>• SmartSeries with Alternate Page selector</li><li>• 8-ohm speaker output with SmartVolume</li></ul>
Weather Rating	NEMA Type 12

## Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	12 lb
Width	8.31 in

## Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

## Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

## Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)  
[Literature - ICS Indoor Stations](#)  
[Specifications - 815161D200](#)