

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # 815-553D200

ICS SmartSeries Indoor Handset/Speaker Multi-party Station, 24 VDC, UL Class I, Div. 2, 8-ohm speaker output with SmartVolume, SmartSeries features with RTU input/output, Gray finish, 25' PVC handset cord



General

Color	Gray
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Type	Multi-Party
	SmartSeries with RTU input & output
	8-ohm speaker output with SmartVolume
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	12 lb
Width	8.31 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	24 VDC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)
[Literature - ICS Indoor Stations](#)