



## Plant Paging Station

By GAI-Tronics  
Catalog # [820-350D100](#)

ICS SmartSeries Outdoor Speaker Amplifier Station - 100-240VAC - UL Class I, Div. 2 - 8-ohm speaker output with SmartVolume - SmartSeries features with RTU input/output - Orange finish



### General

Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Series	ICS
Signal Type	Analog
Type	<ul style="list-style-type: none"><li>• Speaker Amplifier Station</li><li>• Outdoor Speaker Amplifier Stations</li></ul>
Weather Rating	NEMA Type 4X

### Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in
Height	14.6 in
Weight	13 lb
Width	10.9 in

### Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

### Product Assets

[Installation Manuals - ICS Class I, Div. 2 Weatherproof Page/Party® Station](#)  
[Literature - ICS Amplifiers](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
GTC-820-350D100-SPEC-EN | REV 7/2023