

Plant Paging Station

By GAI-Tronics
Catalog # [820-350D100](#)

ICS SmartSeries Outdoor Speaker Amplifier Station - 100-240VAC - UL Class I, Div. 2 - 8-ohm speaker output with SmartVolume - SmartSeries features with RTU input/output - Orange finish



Features

Industrial Communication System

General

Catalog Number	820-350D100
Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	• Speaker Amplifier Station • Outdoor Speaker Amplifier Stations
Weather Rating	NEMA Type 4X

Dimensions

Cubic Capacity	1670.97 cu.in
----------------	---------------

Depth	10.5 in
Height	14.6 in
Weight	13 lb
Width	10.9 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Weatherproof Page/Party® Station](#)
[Literature - ICS Amplifiers](#)
[Specifications - 820350D100](#)