

Plant Paging Station

By GAI-Tronics
Catalog # [820-350D2A4](#)

ICS SmartSeries Offshore Speaker Amplifier Station - 100-240VAC - UL Class I, Div. 2 - 8-ohm speaker output with SmartVolume - SmartSeries features with RTU input/output - Stainless steel terminal box- Gray finish, PCBA tropicalization



Features

Industrial Communication System

General

Catalog Number	820-350D2A4
Color	Gray
Material	GRP / Steel / Stainless steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Type	<ul style="list-style-type: none">Offshore Stations8-ohm speaker output with SmartVolumeSmartSeries features with RTU input & output
Weather Rating	NEMA Type 4X

Dimensions

Cubic Capacity	3774.246 cu.in
Depth	10.5 in
Height	29.2 in
Weight	30 lb
Width	12.31 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Off-Shore Page/Party® Station](#)
[Literature - ICS Offshore Stations](#)
[Specifications - 820350D2A4](#)