

Plant Paging Station

By GAI-Tronics
 Catalog # [820-750D100](#)

ICS SmartSeries Outdoor Speaker Amplifier Station - 24VDC - UL Class I, Div. 2 - 8-ohm speaker output with SmartVolume - SmartSeries features with RTU input/output - Orange finish



Features

Industrial Communication System

General

Catalog Number	820-750D100
Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	- Speaker Amplifier Station - Outdoor Speaker Amplifier Stations
Weather Rating	NEMA Type 4X

Dimensions

Cubic Capacity	1670.97 cu.in
----------------	---------------

Depth	10.5 in
Height	14.6 in
Weight	13 lb
Width	10.9 in

Electrical Ratings

Input Voltage	24 VDC
Signal	33 Ohm
Voltage Rating	24 VDC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Weatherproof Page/Party® Station](#)
[Literature - ICS Amplifiers](#)
[Specifications - 820750D100](#)