

# Plant Paging/Intercom Station

By GAI-Tronics  
 Catalog # [821-111B100](#)

ICS Outdoor Handset/Speaker Single-party Station, 100-240 VAC, CE Safe area, 8-ohm speaker output, - Orange finish, 6' PVC handset cord

## Features

Industrial Communication System

## General

Catalog Number	821-111B100
Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	<ul style="list-style-type: none"> <li>Single Party</li> <li>8-ohm speaker output</li> </ul>
Weather Rating	IP66

## Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in



Height	14.6 in
Weight	13 lb
Width	10.9 in

## Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

## Certifications And Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

## Product Assets

[Installation Manuals - ICS Weatherproof Page/Party® Handset/Speaker Amplifier Station](#)  
[Literature - ICS Outdoor Stations](#)  
[Specifications - 821111B100](#)