

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # 821-111B1A0

ICS Outdoor Handset/Speaker Single-party Station - 100-240VAC - CE Safe area - 8-ohm speaker output - Orange finish, 6' PVC handset cord, PCBA tropicalization



General

Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	Single Party
	8-ohm speaker output
Weather Rating	IP66

Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in
Height	14.6 in
Weight	13 lb
Width	10.9 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

Product Assets

[Installation Manuals - ICS Weatherproof Page/Party® Handset/Speaker Amplifier Station](#)
[Literature - ICS Outdoor Stations](#)