

Plant Paging/Intercom Station

By GAI-Tronics

Catalog # 821-111C501

ICS Hazardous Area Handset/Speaker Single-party Station - 100-240 VAC - UL Class I, Div. 1, 8-ohm speaker output - Gray finish, 6' PVC handset cord



General

Color	Gray
Material	Aluminum
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Weather Rating	NEMA Type 4X

Dimensions

Cubic Capacity	2182.858848 cu.in
Depth	11.68 in
Height	14.31 in
Weight	49 lb
Width	13.06 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 1

Product Assets

[Installation Manuals - ICS Hazardous Area Page/Party® Station](#)
[Literature - ICS Hazardous Area Stations](#)