



## Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # [825-111B2A0](#)

ICS Outdoor Handset/Speaker Multi-party Station - 100-240VAC - CE Safe area - 8-ohm speaker output - Gray finish, 6' PVC handset cord, PCBA tropicalization



### General

Color	Gray
Material	GRP / Steel
Output Level Speaker	8 Ohm
Series	ICS
Signal Type	Analog
Weather Rating	IP66

### Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in
Height	14.6 in
Weight	13 lb
Width	10.9 in

### Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications and Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

### Product Assets

[Installation Manuals - ICS Weatherproof Page/Party® Handset/Speaker Amplifier Station](#)  
[Literature - ICS Outdoor Stations](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
GTC-825-111B2A0-SPEC-EN | REV 7/2023