



Plant Paging/Intercom Station

By GAI-Tronics
Catalog # [825-121D100](#)

ICS Outdoor Handset/Speaker Multi-party Station - 100-240VAC - UL Class I, Div. 2 - 8-ohm speaker output with VLC - Orange finish, 6' PVC handset cord



General

| | |
|----------------------|--------------|
| Color | Orange |
| Material | GRP / Steel |
| Output Level Speaker | 8 Ohm |
| Series | ICS |
| Signal Type | Analog |
| Weather Rating | NEMA Type 4X |

Dimensions

| | |
|----------------|---------------|
| Cubic Capacity | 1670.97 cu.in |
| Depth | 10.5 in |
| Height | 14.6 in |
| Weight | 13 lb |
| Width | 10.9 in |

Electrical Ratings

| | |
|----------------|-------------|
| Signal | 33 Ohm |
| Voltage Rating | 100-240 VAC |

Certifications and Compliance

| | |
|---------------------|----------|
| Certified Listed | UL |
| Hazardous Rating(s) | UL Div 2 |

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Weatherproof Page/Party® Station](#)
[Literature - ICS Outdoor Stations](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
GTC-825-121D100-SPEC-EN | REV 7/2023