

# Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # [825-111D204](#)

ICS Offshore Handset/Speaker Multi-party Station, 100-240 VAC,  
UL Class I, Div. 2, 8-ohm speaker output, Stainless steel terminal  
box, Gray finish, 6' PVC handset cord



## Features

Industrial Communication System

## General

|                      |  |
|----------------------|--|
| Catalog Number       | 825-111D204  |
| Color                | Gray   |
| Material             | GRP / Steel  |
| Output Level Speaker | 8 Ohm  |
| Power                | 30 W   |
| Series               | ICS  |
| Signal Type          | Analog   |
| Type                 | <ul style="list-style-type: none"><li>Offshore Stations</li><li>8-ohm speaker output</li></ul> |
| Weather Rating       | NEMA Type 4X   |

## Dimensions

|                |               |
|----------------|---------------|
| Cubic Capacity | 1670.97 cu.in |
|----------------|---------------|

|        |         |
|--------|---------|
| Depth  | 10.5 in |
| Height | 14.6 in |
| Weight | 13 lb   |
| Width  | 10.9 in |

## Electrical Ratings

|                |             |
|----------------|-------------|
| Input Voltage  | 100-240 VAC |
| Signal         | 33 Ohm      |
| Voltage Rating | 100-240 VAC |

## Certifications And Compliance

|                     |          |
|---------------------|----------|
| Certified Listed    | UL       |
| Hazardous Rating(s) | UL Div 2 |

## Product Assets

[Installation Manuals - ICS Off-Shore Page/Party® Station](#)  
[Literature - ICS Offshore Stations](#)  
[Specifications - 825111D204](#)