

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # 825-112F303

ICS Hazardous Area Handset/Speaker Multi-party Station - 100-240 VAC - ATEX Zone 2 - 8-ohm speaker output - Black finish, 15' PVC handset cord



General

Color	Black
Material	Polyester, Fiberglass Reinforced
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Weather Rating	IP66

Dimensions

Cubic Capacity	700.170022 cu.in
Depth	5.02 in
Height	11.81 in
Weight	15 lb
Width	11.81 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	ATEX
Hazardous Rating(s)	ATEX Zone 2

Product Assets

[Installation Manuals - ICS Zone 2/22 Weatherproof Page/Party® Station](#)

[Literature - ICS Zone 2 Stations](#)