

## Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # 825-131C5A1

ICS Hazardous Area Handset/Speaker Multi-party Station - 100-240 VAC - UL Class I, Div. 1, 8-ohm speaker output with VLC - RTU relay output - Gray finish, 6' PVC handset cord, PCBA tropicalization



### General

Color	Gray
Material	Aluminum
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Weather Rating	NEMA Type 4X

### Dimensions

Cubic Capacity	2182.858848 cu.in
Depth	11.68 in
Height	14.31 in
Weight	49 lb
Width	13.06 in

### Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 1

### Product Assets

[Installation Manuals - ICS Hazardous Area Page/Party® Station](#)  
[Literature - ICS Hazardous Area Stations](#)