

Plant Paging/Intercom Station

By GAI-Tronics
 Catalog # 825-141D1A4

ICS SmartSeries Offshore Handset/Speaker Multi-party Station, 100-240 VAC, UL Class I, Div. 2, 8-ohm speaker output with SmartVolume, SmartSeries features, Stainless steel terminal box, Orange finish, 6' PVC handset cord, PCBA tropicalization



General

Catalog Number	825-141D1A4
Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Type	<ul style="list-style-type: none"> • Offshore Stations • 8-ohm speaker output with SmartVolume • Multi-Party
Weather Rating	NEMA Type 4X

Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in

Height	14.6 in
Weight	13 lb
Width	10.9 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Off-Shore Page/Party® Station](#)
[Literature - ICS Offshore Stations](#)