

## Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # 825-141D2AO

ICS SmartSeries Outdoor Handset/Speaker Multi-party Station -  
100-240VAC - UL Class I, Div. 2 - 8-ohm speaker output with  
SmartVolume - SmartSeries features - Gray finish, 6' PVC  
handset cord, PCBA tropicalization



### General

Color	Gray
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Weather Rating	NEMA Type 4X

### Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in
Height	14.6 in
Weight	13 lb
Width	10.9 in

### Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

### Product Assets

[Installation Manuals - ICS Class I, Div. 2 Weatherproof  
Page/Party® Station](#)  
[Literature - ICS Outdoor Stations](#)