

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # 825-151D200

ICS SmartSeries Outdoor Handset/Speaker Multi-party Station -
100-240VAC - UL Class I, Div. 2 - 8-ohm speaker output with
SmartVolume - SmartSeries features with RTU input/output -
Gray finish, 6' PVC handset cord



General

Color	Gray
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Weather Rating	NEMA Type 4X

Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in
Height	14.6 in
Weight	13 lb
Width	10.9 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Weatherproof
Page/Party® Station](#)
[Literature - ICS Outdoor Stations](#)