

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # 825-531E502

ICS Hazardous Area Handset/Speaker Multi-party Station - 24 VDC - ATEX Zone 1, 8-ohm speaker output with VLC - RTU relay output - Gray finish, 6' PVC handset cord



General

Color	Gray
Material	Aluminum
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Weather Rating	IP66

Dimensions

Cubic Capacity	2182.858848 cu.in
Depth	11.68 in
Height	14.31 in
Weight	49 lb
Width	13.06 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	24 VDC

Certifications And Compliance

Certified Listed	ATEX
Hazardous Rating(s)	ATEX Zone 1

Product Assets

[Installation Manuals - ICS Hazardous Area Page/Party® Station](#)
[Literature - ICS Hazardous Area Stations](#)