

## Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # 825-531F303

ICS Hazardous Area Handset/Speaker Multi-party Station - 24 VDC - ATEX Zone 2 - 8-ohm speaker output with VLC - RTU relay output - Black finish, 6' PVC handset cord



### General

Color	Black
Material	Polyester, Fiberglass Reinforced
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Weather Rating	IP66

### Dimensions

Cubic Capacity	700.170022 cu.in
Depth	5.02 in
Height	11.81 in
Weight	15 lb
Width	11.81 in

### Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications And Compliance

Certified Listed	ATEX
Hazardous Rating(s)	ATEX Zone 2

### Product Assets

[Installation Manuals - ICS Zone 2/22 Weatherproof Page/Party® Station](#)

[Literature - ICS Zone 2 Stations](#)