

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # [830-410B100](#)

ICS Remote Handset/Speaker Amplifier Station, 100-240 VAC,
8-ohm speaker output, Orange finish, CE Safe Area



General

| | |
|----------------------|--|
| Color | Orange |
| Material | Steel |
| Output Level Speaker | 8 Ohm |
| Series | ICS |
| Signal Type | Analog |
| Type | Remote Handset/Speaker Amplifier Station |
| Weather Rating | NEMA Type 12 |

Dimensions

| | |
|----------------|----------------|
| Cubic Capacity | 985.6491 cu.in |
| Depth | 8.18 in |
| Height | 14.5 in |
| Weight | 11 lb |
| Width | 8.31 in |

Electrical Ratings

| | |
|----------------|-------------|
| Signal | 33 Ohm |
| Voltage Rating | 100-240 VAC |

Certifications and Compliance

| | |
|---------------------|--------------|
| Certified Listed | CE |
| Hazardous Rating(s) | CE Safe Area |

Product Assets

[Installation Manuals - ICS Remote Subset Page/Party® Handset/Speaker Amplifier Station](#)
[Literature - ICS Remote Stations](#)