

## Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # [830-450A1R0](#)

ICS Remote Handset/Speaker Amplifier Station, 100-240 VAC, 70/100V speaker output, SmartSeries features with RTU input/output, Orange finish, UL Safe area



### General

Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Series	ICS
Signal Type	Analog
Type	Remote Handset/Speaker Amplifier Station
Weather Rating	NEMA Type 12

### Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	11 lb
Width	8.31 in

### Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

### Product Assets

[Installation Manuals - ICS Remote Subset Page/Party® Handset/Speaker Amplifier Station](#)  
[Literature - ICS Remote Stations](#)