

# Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # [830-450A100](#)

ICS Remote Handset/Speaker Amplifier Station,100-240 VAC, 8-ohm speaker output with SmartVolume, SmartSeries features with RTU input/output, Orange finish, UL Safe area



**Features**

Industrial Communication System

**General**

Catalog Number	830-450A100
Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	Remote Handset/Speaker Amplifier Station
Weather Rating	NEMA Type 12

**Dimensions**

Cubic Capacity	985.6491 cu.in
Depth	8.18 in

Height	14.5 in
Weight	11 lb
Width	8.31 in

**Electrical Ratings**

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

**Certifications And Compliance**

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

**Product Assets**

[Installation Manuals - ICS Remote Subset Page/Party® Handset/Speaker Amplifier Station](#)  
[Literature - ICS Remote Stations](#)  
[Specifications - 830450A100](#)