

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # 830-450A1R0

ICS Remote Handset/Speaker Amplifier Station, 100-240 VAC,
70/100V speaker output, SmartSeries features with RTU
input/output, Orange finish, UL Safe area



General

Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	Remote Handset/Speaker Amplifier Station
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	11 lb
Width	8.31 in

Electrical Ratings

Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

Product Assets

[Installation Manuals - ICS Remote Subset Page/Party®
Handset/Speaker Amplifier Station](#)
[Literature - ICS Remote Stations](#)