



# Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # 830-450A2A0

ICS Remote Handset/Speaker Amplifier Station, 100-240 VAC, 8-ohm speaker output with SmartVolume, SmartSeries features with RTU input/output, Gray finish, PCBA tropicalization, UL Safe area

## General

Catalog Number	830-450A2A0
Color	Gray
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	Remote Handset/Speaker Amplifier Station
Weather Rating	NEMA Type 12

## Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in
Weight	11 lb

Width	8.31 in
-------	---------

## Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

## Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

## Product Assets

- [Installation Manuals - ICS Remote Subset Page/Party® Handset/Speaker Amplifier Station](#)
- [Literature - ICS Remote Stations](#)
- [Specifications - 830-450A2A0](#)