

# Plant Paging/Intercom Station

By GAI-Tronics  
 Catalog # [830-840A100](#)

ICS Remote Handset/Speaker Amplifier Station, 24 VDC, 8-ohm speaker output with SmartVolume, SmartSeries features, Orange finish, UL Safe Area

## Features

Industrial Communication System

## General

Catalog Number	830-840A100
Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	Remote Handset/Speaker Amplifier Station
Weather Rating	NEMA Type 12

## Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in



Height	14.5 in
Weight	11 lb
Width	8.31 in

## Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

## Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

## Product Assets

[Installation Manuals - ICS Remote Subset Page/Party® Handset/Speaker Amplifier Station](#)  
[Literature - ICS Remote Stations](#)  
[Specifications - 830840A100](#)