

# Plant Paging/Intercom Station

By GAI-Tronics  
 Catalog # [830-840A1A0](#)

ICS Remote Handset/Speaker Amplifier Station, 24 VDC, 8-ohm speaker output with SmartVolume, SmartSeries features, Orange finish, PCBA tropicalization, UL Safe Area



## Features

Industrial Communication System

## General

|                      |  |
|----------------------|--|
| Catalog Number       | 830-840A1A0                              |
| Color                | Orange                                   |
| Material             | Steel                                    |
| Output Level Speaker | 8 Ohm                                    |
| Power                | 30 W                                     |
| Series               | ICS                                      |
| Signal Type          | Analog                                   |
| Type                 | Remote Handset/Speaker Amplifier Station |
| Weather Rating       | NEMA Type 12                             |

## Dimensions

|                |                |
|----------------|----------------|
| Cubic Capacity | 985.6491 cu.in |
| Depth          | 8.18 in        |

|        |         |
|--------|---------|
| Height | 14.5 in |
| Weight | 11 lb   |
| Width  | 8.31 in |

## Electrical Ratings

|                |             |
|----------------|-------------|
| Input Voltage  | 100-240 VAC |
| Signal         | 33 Ohm      |
| Voltage Rating | 100-240 VAC |

## Certifications And Compliance

|                     |              |
|---------------------|--------------|
| Certified Listed    | UL           |
| Hazardous Rating(s) | UL Safe Area |

## Product Assets

[Installation Manuals - ICS Remote Subset Page/Party® Handset/Speaker Amplifier Station](#)  
[Literature - ICS Remote Stations](#)  
[Specifications - 830840A1A0](#)