

## Plant Paging/Intercom Subset

By GAI-Tronics  
Catalog # [841-008B300](#)

ICS Remote Desktop Single-party Subset, CE Safe area, Black finish, 6' PVC handset cord



### General

Color	Black
Material	ABS (Acrylonitrile butane styrene - Thermoplastic polymer)
Output Level Speaker	16 Ohm
Series	ICS
Signal Type	Analog
Type	Remote Desktop Subset
Weather Rating	NEMA Type 1

### Dimensions

Cubic Capacity	309.82464 cu.in
Depth	4.56 in
Height	8.94 in
Weight	5 lb
Width	7.6 in

### Certifications and Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

### Product Assets

[Installation Manuals - ICS - Page/Party® Desktop Subset](#)  
[Literature - ICS Remote Stations](#)  
[Literature - SP2 - Remote Handset Stations](#)

### Related Products

[VoIP Plant Paging/Intercom Station](#)  
[VoIP Plant Paging/Intercom Station](#)  
[VoIP Plant Paging/Intercom Station](#)