

Plant Paging/Intercom Subset

By GAI-Tronics
Catalog # 841-008A300

ICS Remote Desktop Single-party Subset, UL Safe area, Black finish, 6' PVC handset cord



General

Color	Black
Material	ABS (Acrylonitrile butane styrene - Thermoplastic polymer)
Output Level Speaker	16 Ohm
Power	2W
Series	ICS
Signal Type	Analog
Type	Remote Desktop Subset
Weather Rating	NEMA Type 1

Dimensions

Cubic Capacity	309.82464 cu.in
Depth	4.56 in
Height	8.94 in
Weight	5 lb
Width	7.6 in

Electrical Ratings

Signal	N/A
--------	-----

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

Product Assets

[Installation Manuals - ICS - Page/Party® Desktop Subset](#)
[Literature - SP2 - Remote Handset Stations](#)
[Literature - ICS Remote Stations](#)